


FEATURES

- **20 W power output:**
Provides sufficient power for a wide range of devices
- **Dual output connectors:**
Features USB A and USB C sockets for versatile connectivity
- **High efficiency of 81%:**
Ensures minimal energy loss during operation
- **Load regulation of $\pm 5\%$:**
Maintains stable output voltage under varying load conditions
- **Wide input voltage range (90 V ac to 264 V ac):**
Compatible with different power sources
- **Compact dimensions (61 mm x 41 mm x 28.8 mm):**
Easy to integrate into various setups
- **Energy Efficiency Level VI:**
Meets high energy efficiency standards

RS PRO 20W AC/DC Adaptor, EU Plug

RS Stock No: 642-771



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO AC/DC adaptor is designed to efficiently convert AC power to DC power, providing a reliable power source for various electronic devices. With a compact design, it is ideal for use in both professional and personal settings, ensuring your devices receive stable power.

General Specifications

Efficiency	81 %
Energy Efficiency Level	VI
Input Connector Type	EU Plug
Load Regulation	±5 %
Number of Outputs	2
Output Connector Type	USB A Socket, USB C Socket
Plug Type	EU, UK
Product Type	AC/DC Adaptor
Sub Type	External Power Supply

Electrical Specifications

Adapter Current	0.8 A
Maximum Input Voltage	264 V ac
Minimum Input Voltage	90 V ac
Output Voltage	12 V dc
Power	20 W

Mechanical Specifications

Depth	28.8 mm
Length	61 mm
Width	41 mm

Operation Environment Specifications

Maximum Operating Temperature	40 °C
Minimum Operating Temperature	0 °C

Approvals

Standards/Approvals	CE, GS-TUV EN62368-1, UKCA, UL-CUL 62368-1
---------------------	--