

Datasheet

Laser Level, 670 nm Laser Wavelength

RS Stock number [374-4775](#)



Description:

Patented sight system for a range of up to 40m/130ft - can also be used outdoors with a target plate.
Can be horizontally aligned on uneven surfaces with the adjusting screw.
Epoxy locked horizontal vial for lasting accuracy.
Adjusting screw made of impact resistant plastic.
Sturdy waterproof metal laser housing.

Specifications:

Alignment Level:	Yes
Laser Class:	Class 2
Laser Wavelength:	670 nm
Length:	600 mm
Levelling Accuracy:	+ 5 mm at 10 m
Vial:	Yes
Working Environment:	Indoor