

## FEATURES

- Robust impact driver with interchangeable heads
- Chrome Vanadium Steel Driver
- Chrome Molybdenum Steel Bits
- Ergonomic grip

# RS PRO Interchangeable Parallel; Phillips Screwdriver Set 6 Piece

RS Stock No.: 541-6539



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

From RS PRO, this impact driver has interchangeable flathead and crosshead bits for great versatility. The ergonomic impact driver has a smooth left and right driving action that makes tightening and loosening screws quicker and easier. For stuck screws, force can be applied to the base of the impact screwdriver for greater turning torque than can be generated by hand alone.

## General Specifications

<b>Screwdriver Type</b>	Interchangeable
<b>Number of Pieces</b>	6
<b>Tip Type</b>	Parallel; Phillips
<b>Set Contents</b>	1 pc-1/2" DR. reversible impact driver with black colour finger guide shock-absorbing injection grip (affixed with RS poly label) 1 pc-1/2" dr. to 5/16" hexagon bit coupler (steel sheet with pin ball type) 4 pc-35 mm (5/16") impact driver bits: parallel slotted: 9 mm Phillips: no.2, no.3 and no.4 2 pc-80 mm (5/16") impact driver bits: Phillips: no.2, no.3 Injection case sizes:8" (w) x 3" (d) x 2-3/4" (h)
<b>Applications</b>	Electricians, Auto mechanics, Carpenters, Construction Workers

## Mechanical Specifications

<b>Tip Size</b>	Parallel: 9mm; Phillips: PH2; PH3; PH4; Hexagon Socket Drive: 5/16 x 1/2 in
<b>Blade Material</b>	Chrome Molybdenum Steel (S-2) For Screwdriver Bits
<b>Handle Material</b>	P.P injection
<b>Blade Finish</b>	Satin chrome plated for impact driver, bit coupler and sandblast bits
<b>Hardness</b>	Heat treated to HRC: 35 ~ 54 for impact driver & bit coupler, HRC: 56 ~ 62 for screwdriver bits

