

20 Pack Cable Raceway T Connector for CBMWWD3211 - Cable Management Accessories - 3 Way Raceway Fitting Connectors - T Type Connector - Wiring Duct Tee Connector - UL Rated - TAA

Product ID: CBMWWD3211T



This 20-pack of raceway T-bars works with the StarTech.com CBMWWD3211 raceway system.

Use these cable raceway T-bars with the StarTech.com CBMWWD3211 raceway to join three of them together and make a right-angle T-branch in your office or server room.

Made from sturdy self-extinguishing ABS that's also warp proof, these wiring duct connectors are UL approved with 94HB Flamability (Horizontal Burning) Rating.

Combine this coupler with other StarTech.com CBMWWD3211 raceway system accessories to give your cable management solution a finished look.

The Coupler (CBMWWD3211C) (20-Pack), joins two raceways together and extends the length of your raceway.

The End Piece (CBMWWD3211E) (20-Pack), cleanly caps off the end of your raceway.

The Inside Elbow (CBMWWD3211I), joins two raceways together inside of corners at 90 degree angle.

The Lateral Elbow (CBMWWD3211L), joins two raceways together and runs them up the wall at a 90 degree angle.

The Outside Elbow (CBMWWD3211O) (20-Pack), joins two raceways together around corners at a 90 degree angle.

These cable management raceway outside elbows are TAA compliant and backed by a StarTech.com Lifetime warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

Certifications, Reports and Compatibility



Applications

- Protects cables from damage while neatly routing them in your office or server room

Features

- **GIVE YOUR CABLE MANAGEMENT RACEWAY A FINISHED LOOK:** Use Cable Raceway T-Connectors (20 pack) to join three StarTech.com CBMWWD3211 raceways together and make a right-angle T-branch in your workspace
- **INDUSTRIAL STRENGTH:** Made from sturdy warp-proof ABS, these T-Connectors are UL approved with UL 94HB Flamability (Horizontal Burning) Rating, self-extinguishing
- **OTHER RACEWAY ACCESSORIES:** Coupler (CBMWWD3211C), End Piece (CBMWWD3211E), Inside Elbow (CBMWWD3211I), Lateral Elbow (CBMWWD3211L), Outside Elbow (CBMWWD3211O); sold separately
- **TECHNICAL SPECIFICATIONS:** 90 Angle Connector Width: 1.26" (32mm) Connector Height: 0.43" (11mm) White UL approved UL 94HB rated RoHS
- **STARTECH.COM ADVANTAGE:** IT professionals choice for over 30 years; These wiring duct fitting tee type connectors are backed for life by StarTech.com, including free 24/5 multi lingual tech support

Physical Characteristics

Warranty	2 Years
Color	White
Material	ABS
Product Length	2.6 in [6.6 cm]
Product Width	3.8 in [9.7 cm]
Product Height	0.5 in [1.3 cm]
Weight of Product	0.3 oz [8.0 g]

Packaging Information

Package Quantity	1
Package Length	7.5 in [19.0 cm]

Package Width	10.4 in [26.5 cm]
Package Height	2.8 in [7.2 cm]
Shipping (Package) Weight	6.3 oz [178.0 g]

What's in the Box

Included in Package	20 - T-Connectors
---------------------	-------------------

**Warranty
Information**

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***