

Product Information

82 02 150

KNIPEX TwinGrip

Front and side gripping pliers



- Gripping, tightening and loosening screws with worn heads and drives
- Unique combination: front and side gripping function, box joint, push-button adjustment
- Biting front jaw with robust teeth and high transmission ratio at the tip of the jaw
- Very slim pliers: Work even in confined spaces, with a narrow turning zone for fast screwing.
- Pinch guard prevents operators' fingers being pinched
- Durable and resilient thanks to robust, box-type pliers joint
- Small and handy – also suitable for more delicate work
- Large front and side gripping capacities: for diameters and width across flats 3 – 16 mm
- Reliable, frontal gripping of flat workpieces up to 6 mm thanks to three-point system
- Three-way adjustable slip joint with push button adjustment for precise alteration of gripping capacity

General	
Part No.	82 02 150
EAN	4003773089360
Pliers	grey atramentized
Head	polished
Handles	with comfort handles
Weight	278 g
Dimensions	150 x 45 x 18 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Adjustment positions	3
Capacities for pipes (diameter)	Ø 0 1/8 - 0 5/8 Inch
Capacities for pipes (diameter)	Ø 3 - 16 mm
Capacities for nuts	3 - 16 mm
Capacities for nuts	0 1/8 - 0 5/8 Inch

Technical changes and errors excepted



