



Datasheet

RS PRO FULLY-COATED BALL-LOCK STAINLESS STEEL CABLE TIES, RED

RS Stock No. 1834215~1834222 (see below)

EN



Technical Information:

Material: Stainless Steel Grade 316

316 grade stainless steel, for extra corrosive environments

Coating: Polyester

Working Temp.: -80°C to +150°C

Description: Entirely Red

Flammability: Fireproof

Other Properties: UV-resistant, Halogen free, non toxic

Product Feature: Fully coated version with non-toxic, halogen free polyester coating, preventing static electricity.

Provide additional edge protection.

Prevent the corrosion between dissimilar materials.

Applications: Ideal for petrochemical, industries, power stations, mining, ship-building, offshore, and other aggressive environments.

Specification

RS CODE	EASE CODE	LENGTH		WIDTH		THICKNESS		MAX. BUNDLE DIAMETER		MIN. TENSILE STRENGTH	
		mm	inch	mm	inch	mm	inch	mm	inch	N	lbs
1834215	CT-SS-BL-100/4.6FC-RD	100	3.9	4.6	0.18	0.35	0.014	25	1.00	900	200
1834216	CT-SS-BL-125/4.6FC-RD	125	4.9					31	1.23		
1834217	CT-SS-BL-150/4.6FC-RD	150	5.9					37	1.46		
1834218	CT-SS-BL-200/4.6FC-RD	200	7.9					50	1.97		
1834219	CT-SS-BL-360/4.6FC-RD	360	14.2					90	3.55		
1834221	CT-SS-BL-200/7.9FC-RD	200	7.9	7.9	0.31	0.35	0.014	50	1.97	1200	270
1834222	CT-SS-BL-360/7.9FC-RD	360	14.2					90	3.55		