2514 : Bending pliers with knee protection
























The + product :

Comfortable: the soft plastic protective pad provides maximum comfort for the knee while bending.
Practical: double marks to see bending angle and do a quick measure of the pipe length.
Durable: the independent roller in zamac avoids rapid wear of the arm and doesn’t hurt pipe.

Description

Suitable for many applications: bending of sanitary or heating pipe, gas supply pipe.

Bended material: copper pipe and multilayer pipe.
A curve allows to put knee. The soft plastic pad is fixed into the curve to provide maximum comfort.
Bending with low effort with the long arms and ergonomic handles.
To reduce pain while repeated bending, lock the bending plier in a bench vice thanks to the two flat surfaces.
Save weight in toolbox with the body in lightweight alloy - aluminium.
Marks on former to see bending angle (45°, 90°, 135°, 180°).
Marks on fix arm for a quick measure of the pipe.

For hardened and annealed copper pipes: Ø 12 to 16 mm / wall thickness: 1 to 1.2 mm.
Bending radius: approx. 3.85 D.
180° bending angle.

Each bending plier is delivered with one protective pad for knee. Pad is also available by unit in spare part (ref. 251405).

More Information

Tips	Stress and pain on the knee are significantly reduced compared to a bending plier without protection. Protection pad in plastic (ref. 251405) which combines flexibility and durability for optimum comfort. Can be assembled easily and with no tool on VIRAX bending pliers range 2514 from model 2023.

References

Sku	Pipe O.D. mm	Bending radius mm	kg
251412	12	45	1,040
251414	14	50	1,320
251416	16	60	1,860