

Datasheet

RS Pro Emergency Light Fitting 2 x 10 W Halogen 350 x 300 x 115 mm

RS Stock No: **494-7874**



Product Details

RS Pro emergency light fitting is suitable for applications such as corridors, workshops and permanently illuminated emergency exit signs. It is powered by 2 x 6V 12Ah batteries.

Features and Benefits

- 'Optional' - Switch for testing emergency mode
- Powered by 2 x 6 V 12Ah batteries
- Battery cut-off prevents deep discharge
- LED indication of battery charge status
- Alarm output contacts
- Supplied with full instructions



ENGLISH

Specifications:

Anti-corrosive	No
Depth	115 mm
Dimensions	350 x 300 x 115 mm
Duration	3 h
Fitting Type	Twin Spot
Lamp Supplied	Yes
Lamp Type	Halogen
Length	350 mm
Luminosity	200 lm
Maintained	Non Maintained
Standards Met	CE Certified
Wattage	2 x 10 W
Width	300 mm
Case Material	PC

For 0.2 Lux

Mounting Height (mtrs)	Spacing to Wall	Between Units
2.5	4	10
4.0	5	12
6.0	6	12
8.0	6	14

For 1 Lux

Mounting Height (mtrs)	Spacing to Wall	Between Units
2.5	2	6
4.0	3	7
6.0	2	7
8.0	1	6

Each unit is fitted with two swivel mounted projectors fitted with 10 watt 12 volt tungsten halogen lamps with a light output of 120 lumens per lamp. The projector has a 30 degree beam spread.

Note: To prevent glare the luminaires should be mounted 30 degrees above the line of sight.