

C470 - Hi-Vis Two Band & Brace Vest

Collection: Vest-Port

Range: High Visibility

Shell Fabric: 100% Polyester, Warp Knit 125g

Product information

The best selling C470 with classic reflective tape configuration will ensure you are seen. Available in all three EN ISO 20471 conforming colours.

Standards

EN ISO 20471 Class 2
RIS 3279 TOM Issue 2 (Orange Only)
ANSI/ISEA 107 TYPE R CLASS 2

Vest-Port

The Vest-Port™ extensive range of vests covers the varied demands of the work environment from core styles to the revolutionary "Executive" design, which is now available in both summer and winter weights.

High Visibility

Our extensive range of High-Visibility clothing meets stringent requirements in both design and construction, to ensure compliance with the latest EN ISO 20471 & ANSI standards. Innovative and technical, our High Visibility range is ideal for those who will not compromise on style, comfort, protection and performance.

Features

- Lightweight and comfortable
- Reflective tape for increased visibility
- Hook and loop closure for easy access
- Generous fit for wearer comfort
- Certified to EN ISO 20471 after 50x washes
- Complies with RIS 3279-TOM for rail industry (orange only)
- CE certified
- Available in sizes up to 7XL



Orange S/M-6XL/7XL,
Yellow S/M-6XL/7XL,
Red S/M-XXL/3XL

PORTWEST®

PRODUCT SPECIFICATION & TECHNICAL DATA

C470 - Hi-Vis Two Band & Brace Vest

Commodity Code: 6110309100

Test House

Cert No: PORTWE.A041514A

Cert No: 2777_13422_01_E00_00

Wash Care



CARTON DIMENSIONS/WEIGHT

Item	Colour	Len	Wid	Hgt	Weight (Kg)	Cubic (m ³)	EAN13	DUN14
C470ORRS/M	Orange	43.0	28.0	55.0	0.1630	0.0662	5036108141647	15036108613264
C470ORRL/XL	Orange	43.0	28.0	55.0	0.1780	0.0662	5036108141654	15036108613257
C470ORRXX/3X	Orange	43.0	28.0	55.0	0.1860	0.0662	5036108141661	15036108613271
C470ORR4X/5X	Orange	43.0	28.0	58.0	0.1990	0.0698	5036108141678	15036108613240
C470ORR6X/7X	Orange	43.0	28.0	58.0	0.2190	0.0698	5036108256273	15036108745187