

Plastic cable markers - KMK 3 - 1005211

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Plastic cable marker, for cables from 16 to 31 mm diameter, labeling with insert strips ESL..., EST... or large format ES/KMK 3-GB, lettering field size: 40 x 17 mm

Your advantages

- ✔ Labeling service: Phoenix Contact can custom-label all insert labels for plastic cable markers according to your requirements
- ✔ The printed insert label is protected from dirt by the sealing cap
- ✔ Plastic cable markers for marking and bundling conductors and cables indoors

RoHS

Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 017918 012441
GTIN	4017918012441
Weight per Piece (excluding packing)	5.600 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	40 mm
Width (a)	17 mm
Height (c)	17 mm
Cable diameter	16 mm ... 35 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

General

Color	transparent
-------	-------------

Plastic cable markers - KMK 3 - 1005211

Technical data

General

Type	Mounting set
Components	free from silicone and halogen
Material	Polyethylene
Marking mounting type	Assembly with cable binders

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001530
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504

Accessories

Accessories

Conductor marking

Plastic cable markers - KMK 3 - 1005211

Accessories

Insert label - EMT (40X17)R - 0817293



Insert label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: insert, cable diameter range: 16 ... 35 mm, lettering field size: 40 x 17 mm

Device marking

Snap-in markers - US-EMP (40X17) - 0829437



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 40 x 17 mm

Labeled conductor marker

Insert label - EMT (40X17)R CUS - 0824385



Insert label, can be ordered: by line, white, labeled according to customer specifications, mounting type: insert, cable diameter range: 16 ... 35 mm, lettering field size: 40 x 17 mm

Labeled terminal marker

Insert strip - ESL 40X17 CUS - 0824403



Insert strip, can be ordered: Sheet, white, labeled according to customer specifications, mounting type: insert, lettering field size: 40 x 17 mm

Terminal marking

Insert strip - ESL 40X17 - 0808095



Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems, perforated, mounting type: insert, lettering field size: 40 x 17 mm

