

Product Data Sheet uvex Dispenser „one 2 click“

UVEX ARBEITSSCHUTZ GmbH, Würzburger Str. 181-189, D-90766 Fürth

Product characteristics:

- Easy-to-use, robust wall-mounted dispenser
- Easy installation and a controlled release mechanism which ensures the correct number of plugs are dispensed
- The transparent design makes it easy to monitor the number of earplugs remaining
- The collecting tray catches the earplugs
- Installed at a convenient location, the dispenser has sufficient capacity to supply large production areas with hearing protection at a favourable price
- Dispenser for 600 pairs uvex disposable earplugs



Dispenser can be filled with following disposable plugs:

Art.-No. 2112.022 uvex x-fit	300 pairs loose in refill box
Art.-No. 2112.023 uvex com4-fit	300 pairs loose in refill box
Art.-No. 2112.061 uvex xtra-fit	250 pairs loose in refill box
Art.-No. 2112.118 uvex hi-com lime	300 pairs loose in refill box
Art.-No. 2112.119 uvex hi-com beige	300 pairs loose in refill box
Art.-No. 2124.003 uvex xact-fit	400 pairs loose in refill box
Art.-No. 2124.013 uvex xact-fit detec	400 pairs loose in refill box

Material:

Earplug container: SBC
Mounting: PP
Barrel with ratch wheel: PP
Collecting tray: PP

Weight & Dimensions:

Weight: 1,1 kg
Dimensions: height: 475mm width: 165mm depth: 190mm

Version/Colour:

Article-No.	Colour	Retail unit
2112.000	transparent/grey/sky-blue	1 Dispenser

Attenuation Data earplugs:

uvex x-fit

SNR: 37 dB (A)	H: 36dB(A)	M: 34dB(A)	L: 34dB(A)
----------------	------------	------------	------------

f/Hz	63	125	250	500	1000	2000	4000	8000
MA dB(A)	35,3	38,4	39,3	40,8	38,9	37,8	45,9	45,1
SD dB(A)	4,2	6,3	5,3	5,5	5,5	4,3	3,9	4,6
APV dB(A)	31,1	32,1	34,0	35,3	33,4	33,5	42,0	40,5

uvex com4-fit

SNR: 33 dB (A)	H: 33dB(A)	M: 30dB(A)	L: 29dB(A)
----------------	------------	------------	------------

f/Hz	63	125	250	500	1000	2000	4000	8000
MA dB(A)	28,9	31,0	33,6	33,8	33,6	36,2	40,6	44,3
SD dB(A)	3,4	5,2	5,4	5,4	4,0	4,2	3,7	2,9
APV dB(A)	25,5	25,8	28,2	28,4	29,6	32,0	36,9	41,4

uvex xtra-fit

SNR: 36 dB (A)	H: 34dB(A)	M: 33dB(A)	L: 32dB(A)
----------------	------------	------------	------------

f/Hz	63	125	250	500	1000	2000	4000	8000
MA dB(A)	32,7	34,8	36,8	38,9	36,9	36,2	44,0	41,5
SD dB(A)	4,6	4,4	5,6	5,2	4,7	3,7	4,0	5,0
APV dB(A)	28,1	30,4	31,2	33,7	32,2	32,5	40,0	36,5

uvex hi-com

SNR: 24 dB (A)	H: 26dB(A)	M: 20dB(A)	L: 18dB(A)
----------------	------------	------------	------------

f/Hz	63	125	250	500	1000	2000	4000	8000
MA dB(A)	17,5	20,0	20,4	22,8	24,6	31,2	37,5	40,3
SD dB(A)	6,4	2,9	3,2	4,7	5,1	5,0	5,9	6,6
APV dB(A)	11,2	17,0	17,2	18,7	19,5	26,2	31,6	33,7

uvex xact-fit / uvex xact-fit detec

SNR: 26 dB (A)	H: 28dB(A)	M: 23dB(A)	L: 19dB(A)
----------------	------------	------------	------------

f/Hz	63	125	250	500	1000	2000	4000	8000
Dämm. dB(A)	16,6	19,4	22,0	25,6	27,5	31,8	34,4	36,9
SD dB(A)	5,4	4,9	4,2	4,9	4,7	3,8	4,4	6,0
APV dB(A)	11,2	14,5	17,8	20,7	22,8	28,0	30,0	30,9