

## FEATURES

- Titanium Nitride Coated (TiN)
- Longer shaft length
- Right angle cutting tip
- 118° cutting angle
- Available in sizes from 0.25mm – 20mm

## RS PRO HSS Twist Drill Bit, 7mm x 109mm

RS Stock No.: 214-240



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

High speed titanium nitride coated jobber drill bits, suitable for a multitude of jobs and materials feature a longer shaft compared to other standard drill bits and can be used in both hand and machine drills. Suitable for drilling metal, wood and plastic along with a range of other materials, jobber drill bits feature right hand cutting tip with 118° cutting angle.

### General Specifications

<b>Drill Bit Type</b>	Twist Drill Bit
<b>Type</b>	Twist
<b>Material</b>	HSS
<b>Surface</b>	Tin-coated
<b>Drilling Application</b>	Metals, woods, plastics

### Mechanical Specifications

<b>Overall Length</b>	109mm
<b>Point Angle</b>	118°
<b>Diameter</b>	7mm

### Approvals

<b>Compliance/Certifications</b>	DIN 338; BS 328-ISO 235/1
----------------------------------	---------------------------





RS Stock No.	Dia.(mm)	Overall Length(mm)	Flute Length(mm)
213-887	1.0	34	12
213-900	1.1	36	14
213-310	1.2	38	16
213-893	1.3	38	16
213-376	1.4	40	18
213-871	1.5	40	18
213-859	1.6	43	20
213-433	1.7	43	20
213-865	1.8	46	22
213-972	1.9	46	22
213-916	2.0	49	24
213-966	2.1	49	24
213-950	2.2	53	27
213-944	2.3	53	27
213-938	2.4	57	30
213-922	2.5	57	30
213-843	2.6	57	30
213-764	2.7	61	33
213-758	2.8	61	33
213-427	2.9	61	33
213-411	3.0	61	33
213-382	3.1	65	36
213-405	3.2	65	36
213-398	3.3	65	36
213-742	3.4	70	39
213-304	3.5	70	39
213-720	3.6	70	39
213-714	3.7	70	39
213-736	3.8	75	43
213-837	3.9	75	43