

1/2" 12-POINT SOCKETS - METRIC | E117059



Description

- ISO 2725-1 - DIN 3124 - ISO 1174-1 - ISO 1711-1 - ISO 691
- Chrome vanadium steel.
- OGV® profile: tightening torque applied to the sides rather than to the angles of the nut.
- High Chrome finish.
- For manual use.

Information

EAN	3258951170595
A [mm]	16
d1 [mm]	23.3
d2 [mm]	22.5
H [mm]	36.5
L [mm]	38
L1 [mm]	14
Conditioning	1
[g]	66

