

WorkForce DS-510

DATASHEET



The WorkForce DS-510 is a document scanner, designed for a variety of demanding organisations and sectors, such as government, bank, healthcare and small businesses. With high scanning speeds and fast data processing features, this sheetfed scanner is ideal for easy document workflow. Multiple users can share the WorkForce DS-510 and benefit from PushScan features using the optional Network Interface Box.

High-speed scanner

This document scanner features a compact footprint and high speed scanning of up to 26ppm / 52ipm, even at 200 and 300dpi in colour or monochrome. This, combined with hardware JPEG compression, makes large scan jobs faster to process. With the optional Network Interface Unit¹, the WorkForce DS-510 is ideal for sharing across office/department networks.

Document workflow

Epson Document Capture Pro makes it easy to integrate this business scanner into your document management system, speeding up workflow and enabling you to capture, convert and distribute scanned information into your document repositories. In addition, barcode recognition and Zonal OCR will help automate large document processes, such as file naming and folder creation. The WorkForce DS-510 is easy to integrate thanks to TWAIN, ISIS and WIA driver support.

Efficient

Epson Scan software offers a wide range of advanced document imaging features, including multi-document size detection, text enhancement and automatic de-skew to improve efficiency and increase productivity.

Network sharing

Share between multiple users using the optional Network Interface Unit. Combined with Document Capture Pro software, the Network Interface Unit allows you to customise 'scan to' job commands, such as 'scan to' Microsoft SharePoint™ among others, from the scanner's panel.

KEY FEATURES

- **High-speed scanner**
Up to 26ppm / 52ipm
- **Easy integration**
Epson Document Capture Pro compatibility
- **Hassle-free**
Advanced feed technology
- **Network capable**
Optional Network Interface Unit
- **Eco-friendly**
ENERGY STAR-qualified¹

PRODUCT SPECIFICATIONS

TECHNOLOGY

Scanner type	Sheetfed Scanner
Scanning Resolution	600 dpi x 600 dpi (Horizontal x Vertical)
ADF Maximum Document Size	215 mm x 914 mm (Horizontal x Vertical)
Paper Formats	A3 with stitching function, A4, A5, A6, B5, B6, Letter, Postcard, Business cards, Plastic cards, Legal, Executive
Color Depth	Input: 48 Bits Color / 16 Bits Monochrome, Output: 24 Bits Color / 8 Bits Monochrome
Ultrasonic Sensor	Yes

SCANNER

Light Source	ReadyScan LED technology
LCD Display	Optional Epson Network Interface Unit

SCAN SPEED

Scanning Speed	Monochrome: 26 Pages/min - Colour: 26 Pages/min measured with Size: A4 , Resolution: 200 / 300 dpi, Monochrome: 52 image/min - Colour: 52 image/min measured with Size: A4 , Resolution: 200 / 300 dpi
----------------	--

PAPER / MEDIA HANDLING

ADF Paper Setting Capacity	50 Sheets
Reliability Daily Duty Cycle	3,000 Pages
Duplex Scan	Yes
ADF Paper weight	Auto loading: 50 - 130 g/m ² , Manual loading: 50 - 130 g/m ²
Automatic Document Feeder Type	Single pass dual scanning

SCANNING FEATURES

Features	Skip blank page, A3 stitching, Punch holes removal, Pre-defined scanning settings, Automatic area segmentation, Automatic de-skew, Automatic multi-document recognition, Dual Image Output (Windows only), Auto-rotation, Text enhancement, Unsharp Mask (USM), Descreening, Automatic Folder Creation, Barcode Recognition, Manual / Automatic Job Separation, Full Zonal OCR
Output formats	JPEG, TIFF, multi-TIFF, PDF, searchable PDF, secure PDF, PDF/A
File compression features	Hardware JPEG compression, TIFF Compression (JPEG(7) , CITT G4, LZW), PDF Compression

OTHER

Warranty	12 months On site service Optional warranty extension available
----------	--

LOGISTICS INFORMATION

SKU	B11B209301BY
EAN code	8715946527109
Dimensions Single Carton	412 x 278 x 284 mm
Carton Weight	2.43 Kg
Multiple Order Quantity	1 Units
Pallet Size Euro	49 Units
Pallet Size Block	70 Units

WorkForce DS-510

WHAT'S IN THE BOX

- Driver and utilities (CD)
- Main unit
- Power cable
- Setup guide
- USB cable
- Warranty document

OPTIONAL ACCESSORIES

- Network Interface Unit
B12B808451BY
- Roller Assembly Kit
B12B813561
- Carrier Sheet x 5
B12B813431



For more information please contact:

Telephone: 01952 607111 (UK)+
01 436 7742 (Republic of Ireland)
E-mail: enquiries@epson.co.uk
Chat: etalk.epson-europe.com
Fax: 0871 222 6740
+ Local call rate.

Web: www.epson.co.uk
www.epson.ie

1. ENERGY STAR qualification for non-networked models only, when not using Network Interface Panel

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.

EPSON®