

Schneideisenhalter



Stocks for Circular Dies



Art. 600 GD

DIN 225 = EN 22568 zur direkten Aufnahme von Schneideisen nach DIN 223 / 5158 - EN 22568, EN 24230, EN 24231. Aus Zinkdruckguss (GD).

DIN 225 = EN 22568 for directly holding screwing dies in conformity with DIN 223 / 5158 - EN 22568, EN 24230, EN 24231. Made of zinc pressure casting (GD).

CODE	 	M	Mf	Ww	G	mm	g	EAN-CODE 4026558.....
04931	16 x 5	M 1	- M 2,6	1/16 - 3/32		160	50	049311
04932	20 x 5	M 3	- M 4	1/8 - 5/32		200	60	049328
04933	20 x 7	M 4,5	- M 6	3/16 - 1/4		200	60	049335
04934	25 x 9	M 7	- M 9	5/16	G 1/16	224	105	049342
04935	30 x 11	M 10	- M 11	3/8 - 7/16	G 1/8	280	190	049359
04936	38 x 14	M 12	- M 14	1/2 - 9/16		315	315	049366
04937	38 x 10	MF 10	- MF 13		G 1/4	315	330	049373
04938	45 x 18	M 16	- M 20	5/8 - 3/4		450	630	049380
04939	45 x 14	MF 16	- MF 20		G 3/8 - G 1/2	450	640	049397
04940	55 x 22	M 22	- M 24	7/8 - 1"		560	900	049403
04941	55 x 16	MF 21	- MF 26		G 5/8 - G 3/4	560	950	049410
04942	65 x 25	M 27	- M 36	1 1/8 - 1 3/8		630	1380	049427
04943	65 x 18	MF 27	- MF 36		G 7/8 - G 1	630	1400	049434