



**Part Number :** [732870450](#)  
**Product Description :** N Type Attenuator, Plug to Jack, Straight, 18 GHz, 2 Watt, 20 dB, without Hex  
**Series Number :** 73287  
**Status :** Active  
**Product Category :** RF / Coaxial Connectors



## Documents & Resources

**Drawings**  
[732870450\\_sd.pdf](#)

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
--------	--------

Category	RF / Coaxial Connectors
Series	73287
Description	N Type Attenuator, Plug to Jack, Straight, 18 GHz, 2 Watt, 20 dB, without Hex
Keyword	Attenuators
Product Name	N
Style	Attenuator
Type	Medium
UPC	198282630074

## Electrical

Attenuation Level (dB)	20
Average Power Max (Watts)	2
Frequency	18 GHz
Impedance	50Ω
VSWR (max)	1.35:1

## Physical

Body Style	Without Hex
Gender	Plug/Jack
Keying to Mating Part	N/A
Orientation	Straight
Packaging Type	Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Wire/Cable Type	N/A