


## **FEATURES**

- Mineral insulation for flexibility
- Durability and high performance
- Insulated hot junction for reduction in electrical interference
- Plain pot seal with a temperature rating of 200°C.

## RS PRO Type K Thermocouple 150mm Length, 1mm Diameter $\rightarrow$ +1100°C

**RS Stock No.: 787-7696** 



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



**Product Description** 


These sensors or probes have a durable construction and feature a stainless steel 310 probe sheath and a PFA insulated lead. The mineral insulated flexible probe sheath can be bent and formed to suit a wide range of applications. The thermocouple has a single element insulated hot junction for a reduction in electrical interference and a plain pot seal with a temperature rating of 200°C.

## **General Specifications**

Thermocouple Type	Туре К
Construction	Flexible mineral insulated probe with stainless steel sheath, plain pot seal & 1 metre extension cable
Measuring Junction	Underground
Application	high pressure and vacuum applications, and able to withstand high levels of vibration

## **Mechanical Specifications**

Probe Diameter	1mm
Probe Length	150mm
Probe Body Material	Stainless Steel
Insulation / Sheath Material	310 Stainless steel
Termination Type	Cable





	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Compensating	•				couc	
VX (KCB)	7/0.2mm	+Green/-White	Green	10 metres	70657082	827-5609
VX (KCB)	7/0.2mm	+Green/-White	Green	25 metres	70641629	219-4551
VX (KCB)	7/0.2mm	+Green/-White	Green	50 metres	70657080	827-5603
VX (KCB)	7/0.2mm	+Green/-White	Green	100 metres	70641630	219-4573
VX (KCB)	7/0.2mm	+Green/-White	Green	200 metres	70657083	827-5612
	.,					
VX (KCB)	13/0.2mm	+Green/-White	Green	10 metres	70657086	827-5621
VX (KCB)	13/0.2mm	+Green/-White	Green	25 metres	70657087	827-5625
VX (KCB)	13/0.2mm	+Green/-White	Green	50 metres	70657090	827-5634
VX (KCB)	13/0.2mm	+Green/-White	Green	100 metres	70651750	762-1152
,						
U (RCA)	7/0.2mm	+Orange/-White	Orange	10 metres	70657096	827-5656
U (RCA)	7/0.2mm	+Orange/-White	Orange	25 metres	70646158	611-7902
U (RCA)	7/0.2mm	+Orange/-White	Orange	50 metres	70657097	827-5659
			<u> </u>			
U (RCA)	13/0.2mm	+Orange/-White	Orange	10 metres	70641641	219-4769
U (RCA)	13/0.2mm	+Orange/-White	Orange	25 metres	70657093	827-5643
U (RCA)	13/0.2mm	+Orange/-White	Orange	50 metres	70657094	827-5647

	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Exten	sion:					
KX	7/0.2mm	+Green/-White	Green	10 metres	70657084	827-5615
КХ	7/0.2mm	+Green/-White	Green	25 metres	70641729	236-3820
KX	7/0.2mm	+Green/-White	Green	50 metres	70657085	827-5619
КХ	7/0.2mm	+Green/-White	Green	100 metres	70646156	611-7889
кх	7/0.2mm	+Green/-White	Green	200 metres	70657088	827-5628
JX	7/0.2mm	+Black/-White	Black	10 metres	70641640	219-4753
XL	7/0.2mm	+Black/-White	Black	25 metres	70657078	827-5592
JX	7/0.2mm	+Black/-White	Black	50 metres	70657079	827-5596
JX	7/0.2mm	+Black/-White	Black	100 metres	70641737	236-3915
JX	7/0.2mm	+Black/-White	Black	200 metres	70657081	827-5606
ТХ	7/0.2mm	+Brown/-White	Brown	10 metres	70641637	219-4703
ТХ	7/0.2mm	+Brown/-White	Brown	25 metres	70641734	236-3870
ТХ	7/0.2mm	+Brown/-White	Brown	50 metres	70657095	827-5653
ТХ	7/0.2mm	+Brown/-White	Brown	100 metres	70651749	762-1146
ТХ	7/0.2mm	+Brown/-White	Brown	200 metres	70657098	827-5662
NX	7/0.2mm	+Pink/-White	Pink	10 metres	70641635	219-4668
NX	7/0.2mm	+Pink/-White	Pink	25 metres	70657091	827-5637
NX	7/0.2mm	+Pink/-White	Pink	50 metres	70657089	827-5631
NX	7/0.2mm	+Pink/-White	Pink	100 metres	70657092	827-5640
	-	-				



T/C Type	Conductors	Length	Termination	+Positive tail wire	-Negative tail wire code	Allied Code	RS order Code
'Κ' 'Κ' 'Κ'	1/0.2mm 1/0.2mm 1/0.2mm 1/0.2mm	1 metre 2 metre 5 metre 10 metre	Mini plug Mini plug Mini plug Mini plug	Green Green Green Green	White White White White	70643600	363-0250 110-4482 123-6306 123-6307
า	1/0.2mm	1 metre	Mini plug	Black	White	70643599	363-0244
า	1/0.2mm	2 metre	Mini plug	Black	White		123-6308
า	1/0.2mm	5 metre	Mini plug	Black	White		123-6309
า	1/0.2mm	10 metre	Mini plug	Black	White		123-6310
'T'	1/0.2mm	1 metre	Mini plug	Brown	White	70643601	363-0266
'T'	1/0.2mm	2 metre	Mini plug	Brown	White		123-6311
'T'	1/0.2mm	5 metre	Mini plug	Brown	White		123-6312
'T'	1/0.2mm	10 metre	Mini plug	Brown	White		123-6313

<b>Т/С Туре</b>	Conductors	Cores	<b>Reel Length</b>	Allied code	RS order code
КХ	1/0.2mm	+Yellow/-Red	25 metres	70656106	814-0030
КХ	1/0.2mm	+Yellow/-Red	50 metres	70656111	814-0049
КХ	1/0.2mm	+Yellow/-Red	100 metres	70656109	814-0042
KX	7/0.2mm	+Yellow/-Red	25 metres	70656110	814-0046
KX	7/0.2mm	+Yellow/-Red	50 metres	70656113	814-0055
KX	7/0.2mm	+Yellow/-Red	100 metres	70656114	814-0058
KX	1/0.3mm	+Yellow/-Red	25 metres	70656104	814-0024
KX	1/0.3mm	+Yellow/-Red	50 metres	70656107	814-0033
KX	1/0.3mm	+Yellow/-Red	100 metres	70656108	814-0036
тх	1/0.3mm	+Blue/-Red	25 metres	70656121	814-0080
тх	1/0.3mm	+Blue/-Red	50 metres	70656126	814-0099
тх	1/0.3mm	+Blue/-Red	100 metres	70656124	814-0092
TX	1/0.2mm	+Blue/-Red	25 metres	70656125	814-0096
TX	1/0.2mm	+Blue/-Red	50 metres	70656128	814-0106
TX	1/0.2mm	+Blue/-Red	100 metres	70656129	814-0109



	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Exter	nsion:					
KX	7/0.2mm	+Green/-White	Green	10 metres	70657084	827-5615
KX	7/0.2mm	+Green/-White	Green	25 metres	70641729	236-3820
KX	7/0.2mm	+Green/-White	Green	50 metres	70657085	827-5619
KX	7/0.2mm	+Green/-White	Green	100 metres	70646156	611-7889
КΧ	7/0.2mm	+Green/-White	Green	200 metres	70657088	827-5628
JX	7/0.2mm	+Black/-White	Black	10 metres	70641640	219-4753
JX	7/0.2mm	+Black/-White	Black	25 metres	70657078	827-5592
JX	7/0.2mm	+Black/-White	Black	50 metres	70657079	827-5596
JX	7/0.2mm	+Black/-White	Black	100 metres	70641737	236-3915
JX	7/0.2mm	+Black/-White	Black	200 metres	70657081	827-5606
ΤХ	7/0.2mm	+Brown/-White	Brown	10 metres	70641637	219-4703
ΤХ	7/0.2mm	+Brown/-White	Brown	25 metres	70641734	236-3870
ΤХ	7/0.2mm	+Brown/-White	Brown	50 metres	70657095	827-5653
ΤХ	7/0.2mm	+Brown/-White	Brown	100 metres	70651749	762-1146
ΤХ	7/0.2mm	+Brown/-White	Brown	200 metres	70657098	827-5662
NX	7/0.2mm	+Pink/-White	Pink	10 metres	70641635	219-4668
NX	7/0.2mm	+Pink/-White	Pink	25 metres	70657091	827-5637
NX	7/0.2mm	+Pink/-White	Pink	50 metres	70657089	827-5631
NX	7/0.2mm	+Pink/-White	Pink	100 metres	70657092	827-5640



Т/С Туре	Conductors	Cores	Reel Length	Allied code	RS order code
J	1/0.2mm	+Black/-White	25 metres	70657194	827-5980
J	1/0.2mm	+Black/-White	50 metres	70657195	827-5984
J	1/0.315mm	+Black/-White	25 metres	70657198	827-5993
J	1/0.315mm	+Black/-White	50 metres	70657199	827-5996
К	1/0.315mm	+Green/-White	25 metres	70657200	827-6000
К	1/0.315mm	+Green/-White	50 metres	70657205	827-6019
т	1/0.315mm	+Brown/-White	25 metres	70657208	827-6028
т	1/0.315mm	+Brown/-White	50 metres	70657206	827-6022
J	1/0.508mm	+Black/-White	25 metres	70657197	827-5990
J	1/0.508mm	+Black/-White	50 metres	70657201	827-6003
К	1/0.508mm	+Green/-White	25 metres	70657203	827-6012
К	1/0.508mm	+Green/-White	50 metres	70657204	827-6016
J	7/0.2mm	+Black/-White	25 metres	70657202	827-6006
к	7/0.2mm	+Green/-White	25 metres	70657207	827-6025
т	7/0.2mm	+Brown/-White	25 metres	70657209	827-6031
Ν	7/0.2mm	+Pink/-White	25 metres	70657210	827-6034