

Datasheet

RS metal, PVC Flexible Cable Conduit, 20mm 10m

RS Stock number 784-0108



Dimensions – mm

RS Item No.	Description	I.D.		O.D. (mm)	Packing
		Inch	mm		
784-0094	PVC covered metal conduit 12mm 25m	1/3	8.2	11	25m / roll
784-0098	PVC covered metal conduit 16mm 25m	1/2	12.6	16.2	25m / roll
784-0108	PVC covered metal conduit 20mm 10m	5/8	16	20	10m / roll
784-0101	PVC covered metal conduit 20mm 25m	5/8	16	20	25m / roll
784-0105	PVC covered metal conduit 25mm 10m	3/4	21	24.4	10m / roll