

PRODUCT-DETAILS

TY29M-5

CABLE TIE 120LB 30IN GREEN NYLON



General Information

Extended Product Type	TY29M-5
Product ID	7TCG009370R0035
EAN	5414363063759
Catalog Description	CABLE TIE 120LB 30IN GREEN NYLON
Long Description	High Performance Cable Tie, Green Color Nylon 6.6, Length of 770mm (30.3 Inches) for Bundle Diameter up to 229mm (9.02 Inches), Width of 6.9mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F)

Ordering

EAN	5414363063759
UPC	786210900445

Container Information

Package Level 1 Units	500 piece
Package Level 1 Width	9.4 in 239 mm
Package Level 1 Height	4.9 in 124 mm
Package Level 1 Depth / Length	33.1 in 841 mm
Package Level 2 Units	20000 piece

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Effective Date	19700304
Number of Batteries	0
Product Name	TY-RAP FASTENING

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY29M-5
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TY29M-5

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

