



## Waterpump Pliers ClassicPlus

- | The indestructible water pump pliers, with safety box joint for highest stress
- | With Nail- & wire holder
- | Double-toothed jaws
- | With mounting for optionally available plastic jaws, for gentle installation
- | Optimum jaw geometry with self-locking serration
- | Gripping capacity 40% above ISO by means of arch-shaped pitch adjustment
- | Cogs additionally induction hardened
- | Finger trap protection for safe work, prevents injuries caused by squeezing
- | Box joint with wide guide surfaces
- | Ideal fulcrum, minimum effort
- | Ergonomic handle position and shape for optimum power transmission
- | Handles coated with plastic
- | Made of special tool steel, forged, oil-hardened

SKU: 1651-12-180-SB

### General Information

#### Waterpump Pliers

"Made in Germany" is a label of quality, accuracy and experience. All these factors play a role in the production of our water pump pliers. All these wrenches are hardened and tempered, drop-forged from chrome vanadium steel and are thus well-suited to the highest demands over long service lifetimes. To ensure safe working, the jaws of the wrenches are double-toothed, the gripping teeth additionally induction-hardened and the tools have an integrated anti-pinch mechanism.



### Prepared for anything

For many heating engineers and plumbers, the exception proves to be the rule – for example, when they are called to deal with burst water pipes. They do not know in advance what to expect. But with the right selection of versatile tools, every problem becomes a routine task. The NWS tool compilation provides the plumber with tools that are just right and durable for every occasion. And if they need to get to grips with large-diameter pipes, they can do just that with the ClassicPlus.

### Downloads

	1651-12-240.jpg		detail_1651-12-240_1002221543.jpg		detail_1651-12-240_1002221444.jpg
	detail_1651-12-240_1002192134.jpg		detail_1651-12-240_1002192140.jpg		VP-1431.jpg

### Technical Data

1651-12-180-SB		
◀▶	Length - mm	180
◀▶	Length - in	7
○	Pipe - Ø mm	30
○	Pipe - Ø in	1
○	Wrench size - mm	35

	Spannweite - mm	40
	Teeth hardness - HRC	55 - 57
	DIN standards - National, European and worldwide	DIN ISO 8976
	Weight - g	190
	Length including self-service packaging - mm	220
	Width including self-service packaging - mm	65
	Height including self-service packaging - mm	13
	Weight self-service packaging - g	10
	Packing unit	6
	Barcode	40 03758 66510 7