



Technical sheet

HEATFLEX HEATED VEST

Description :

The SurfleX® heated vest offers comfort and warmth, perfect for working outdoors or in low-heat environments. With up to **3 heating modes (25° to 45°)**, it adapts to your body shape with an elegant design. Ideal as an underlayer, it is suitable for low-heat indoor spaces and outdoor environments. With **4 adjustable heating zones**, it guarantees between 6 and 8 hours of autonomy. Rechargeable via included cable and adapter for extended use.

FLEECE HEATFLEX HEATED VEST

6 to 8 hours of battery life

Polyester mesh / Lycra

Cable in internal pocket (adapter provided)



Switch to activate and adjust intensity



Red (45°)
White (35°)
Blue (25°)



Adjustable size thanks to zippers on the sides



4 heating zones



HOW TO WEAR THE HEATED VEST?

The heated vest must be worn as an underlayer, under a coat. It can be worn indoors in unheated or very lightly heated environments.

For what uses? For your missions outside or in a warehouse with little or no heating. It may be recommended for people who also have Raynaud's disease.

REFERENCES

Black	T1	CHAUF1
Black	T2	CHAUF2

SIZE

T1 : S/M
T2: L/XL

MATTER

Fabric: 100% Polyester mesh / lycra (Origin: China)


GROSS WEIGHT

300 Grams (T1)

412 Grams (T2)

LOAD TYPE

USB A cable (USB C adapter supplied)



CHARGING TIME

2 hours

PROPERTIES

Powerbank battery not included Specific battery location in the internal zipped pocket.

AUTONOMY

- High heating level, red (45°): 6 to 8 hours
- Medium heating level, white (35°): 8 to 10 hours
- Low heating level, blue (25°): 10 to 12 hours

HEATING ZONE

2 front heating zones
2 back heating zones



NOTICE D'UTILISATION :

1. Plug the external battery into the internal zipped pocket.
2. Press 3 seconds to turn on.
3. Press 1 time to change the mode.
4. Press 3 seconds to turn off.

INTERVIEW

Hand wash recommended, but machine washable at 30°C, minimum spin.

No tumble dryer, bleach or dry cleaning.

Make sure you remove the battery before washing.

Do not twist or wring, you risk damaging the heating systems.

Use a mild detergent without softener.

CARDBOARD DIMENSIONS

Box of 10 pieces

L 60 cm x | 40 cm x h 40 cm | Poids : T1 : 3.865 kg / T2 : 4.985 kg

Customs code: 62079990