

## DIN rail perforated - NS 15 PERF 2000MM - 1401682


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail perforated, Standard profile, width: 15 mm, height: 5.5 mm, acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, length: 2000 mm, color: silver

RoHS

### Key Commercial Data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 020491
GTIN	4017918020491
Weight per Piece (excluding packing)	300.000 g
Custom tariff number	72166190
Country of origin	Germany

### Technical data

#### Dimensions

Height	5.5 mm
Length	2000 mm
Width	15 mm
Hole width	12.20 mm
Hole height	4.20 mm
Drill hole spacing	20.00 mm

#### General

Material	Steel
Coating	galvanized, passivated with a thick layer
Color	silver

#### Standards and Regulations

Test standard	acc. to EN 60715
---------------	------------------

## DIN rail perforated - NS 15 PERF 2000MM - 1401682

### Technical data

#### Standards and Regulations

Connection in acc. with standard	IEC / EN
----------------------------------	----------

### Classifications

#### eCl@ss

eCl@ss 4.0	23150301
eCl@ss 4.1	23150301
eCl@ss 5.0	27141143
eCl@ss 5.1	27141100
eCl@ss 6.0	27400600
eCl@ss 7.0	27400602
eCl@ss 8.0	27400602
eCl@ss 9.0	27400602

#### ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC000212
ETIM 6.0	EC001285
ETIM 7.0	EC001285

#### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708