

4x4 HDMI Matrix Switch with Audio and Ethernet Control - 4K 60Hz

Product ID: VS424HD4K60



This 4x4 HDMI matrix switch lets you share four HDMI video sources between four independent displays or projectors, and switch between which source is active on each display device.

True 4K at 60Hz

The HDMI switcher box provides a high level of audio and video performance, with superior contrast and crisp, clear imagery. With support for resolutions up to 4K 60Hz (4:4:4 pixel format, 8-bit color depth) and HDR, the matrix switch is ideal for conventions or trade shows, restaurants and classroom settings, as well as hospital/medical applications.

Plus, the 4K 60Hz HDMI switch is backward compatible with earlier versions of HDMI, so it's easy to use with your existing devices and displays.

Optimized Functionality

This 4x4 matrix switch is equipped with convenient push-button switching, WebGUI and RS232 control, and also features a front-panel LED display for easy status monitoring.

The HDMI switch box enables you to switch each input, meaning that different A/V sources can be shown on each output, or a single source can be output to all displays.

Ultimate Convenience

The matrix switcher includes a remote control and IR extender module that provides simple control from a distance, and is designed to save space with a standalone or rack-mounting option (ear-mounts included).

VS424HD4K60 is backed by a StarTech.com 2 -year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Output and switch between four A/V sources across four independent displays
- Create versatile 4K digital signage
- Switch between sources and displays in training sessions

Features

- Share and switch four distinct HDMI A/V signals between four separate displays in a matrix configuration
- Enjoy astonishing picture quality with support for Ultra HD resolutions up to 4K 60Hz
- Install the HDMI switcher as a standalone device, or rack-mount it
- EDID management support enables greater compatibility with your video source and display
- Offers remote management capability with the WebGUI interface

Hardware	Warranty	2 Years
	Audio	Yes
	AV Input	HDMI
	AV Output	HDMI
	Cabling	HDMI
	Industry Standards	HDMI 2.0
	Ports	4
	Rack-Mountable	Yes
Performance	Audio Specifications	7.1 Surround Sound
	Bandwidth	18Gbps
	Maximum Digital Resolutions	3840 x 2160 @ 60Hz 4096 X 2160 @ 24Hz
	Supported Resolutions	1920 x 1200 (1080p) 3840 x 2160 (UHD 4K) 4096 X 2160
	Wide Screen Supported	Yes
Connector(s)	Connector A	4 - HDMI (19 pin) Female
	Connector B	4 - HDMI (19 pin) Female
	Connector Type(s)	1 - DB-9 (9 pin, D-Sub) Female
		1 - RJ-45 Female
		1 - IrDA (Infrared, SIR/FIR)
		1 - USB Mini (4 pin)
Indicators	LED Indicators	1 - Power LED
		4 - Active Port LED
Power	Input Current	1.5
	Input Voltage	100 - 240 AC
	Output Current	2.7
	Output Voltage	24 DC
	Power Source	AC Adapter Included
Environmental	Humidity	20-90%
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)

Physical Characteristics	Color	Black
	Enclosure Type	Metal
	Product Height	1.7 in [4.3 cm]
	Product Length	17.2 in [43.7 cm]
	Product Width	6.3 in [16 cm]
	Weight of Product	4.5 lb [2 kg]
Packaging Information	Package Height	3.7 in [95 mm]
	Package Length	20.7 in [52.5 cm]
	Package Width	11.5 in [29.2 cm]
	Shipping (Package) Weight	8.8 lb [4 kg]
What's in the Box	Included in Package	1 - HDMI Matrix Switch
		1 - Remote Control
		1 - IR Receiver
		2 - Mounting Brackets
		1 - Universal Power Adapter (NA/JP, EU, UK, ANZ)
		1 - User Manual

Product appearance and specifications are subject to change without notice.