

Datasheet
Stock No: 112-0090

RS Pro Desk Lamp



Product Details

RS Pro ispot Blade 8W LED Desk Lamp

The RS Pro ispot blade desk lamp follows a modern minimalist design. With a 180 degree adjustable lamp head and 90 degree adjustable lamp arm the light can be adjusted as desired. The ispot blade includes a touch control interface with multi stage dimming colour temperature and brightness. The colour temperature can be tuned from warm white (3000K) to daylight (6500K). The ispot blade incorporates a USB charging outlet ideal for charging electronic devices such as mobile phones. Available in both black (RS 111-9984) and white (RS 112-0090) finishes.

Features and Benefits

- LED desk lamp- 8W
- Adjustable colour temperature
- Warm white 3000K - daylight 6500K
- Dimmable via touch control interface
- Built in USB charging port ideal for charging phones and other digital devices
- Durable plastic housing
- 90° adjustable lamp arm
- 180° adjustable lamp head
- Folds away for easy storage
- Unique protected registered design
- Available in black and white finishes
- Rated life of 30000 hours
- Type G - British BS1363
- 230 V

USB Charging Port

USB charging outlet

Output voltage: 5VDC

Maximum output current: 1A

Standards

BS EN 60598-1+A11

BS EN 60598-2-1

BS EN 60598-2-5

BS EN 62471

BS EN 62493

BS EN 55015+A2

BS EN 61547

BS EN 61000-3-2+A2

BS EN 61000-3-3

**Office Bench Mount**

Watts: 8watt

Output 480 lumens RA80

Maximum Lux 4100lx

270 x 140 x 330mm

Weight 733grams

Life span 30000h

Voltage AC100-240v 50/60Hz