



**Part Number :** [191440002](#)

**Product Description :** InsulKrimp Spade Tongue Terminal for 22-18 AWG Wire, Tape and Reel

**Series Number :** 19144

**Status :** Active

**Product Category :** Ring and Spade Terminals

**Engineering Number :** AA-235-06XT



---

## Documents & Resources

### Drawings

[191440002\\_sd.pdf](#)


### Specifications

[PS-19902-015-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Ring and Spade Terminals
Series	19144
Description	InsulKrimp Spade Tongue Terminal for 22-18 AWG Wire, Tape and Reel
Keyword	Spade Terminal, Spade Terminals
Product Name	InsulKrimp
Style	Spade
Type	Spade Connector, Metric Spade Connector
UPC	800753104594

### Agency

CSA	LR18689
UL	E32244

### Physical

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.695/g
Packaging Type	Adhesive Tape on Reel
Stud Size	2 (M2)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.70mm max.

Wire Size (AWG)	18, 20, 22
Wire Size mm <sup>2</sup>	0.35-0.80

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

### Application Tooling

#### Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880023</u>
Mini-Mac Pneumatic Applicator for Ring and Spade Terminals, 22-18 AWG	<u>638851300</u>