

## FEATURES

- **Sintered Bronze Material:** Provides high strength and wear resistance, ensuring long-lasting performance.
- **15.02 mm Bore Size:** Suitable for precise applications requiring specific shaft dimensions.
- **Flanged Design:** Offers easy installation and secure positioning within assemblies.
- **Dynamic Load Rating of 14 N/mm<sup>2</sup>:** Ensures reliable performance under varying load conditions.
- **Static Load Rating of 50 N/mm<sup>2</sup>:** Capable of handling significant static loads without deformation.
- **ISO 2795 and ISO 9001:2008 Certified:** Meets international quality and performance standards.

## RS PRO 15.02 mm Flanged Plain Bearing

RS Stock No: 529-027



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO flanged plain bearing is designed for applications requiring smooth, low-friction movement. Made from sintered bronze, it offers excellent durability and performance in various industrial settings. The bearing's primary benefit is its ability to support both static and dynamic loads efficiently.

## General Specifications

Bore Size	15.02 mm
Dynamic Load Rating	14 N/mm <sup>2</sup>
Product Type	Plain Bearing
Static Load Rating	50 N/mm <sup>2</sup>
Sub Type	Flanged

## Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	19.05 mm
Width	16 mm

## Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

