



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #2176085-6
EP 9W (S) 68R 5%

TE Part #6-1614958-0
CPF 0805 4R02 0.1% 25ppm 1K RL

TE Part #3-2176315-9
MELF SMA_A 120R 1% 50PPM 0204 0.4 W

TE Part #1-640388-1
11P MTA156 HDR ASSY RN STR F/L W

TE Part #3-1393789-8
V23079A2006B301

TE Part #2-1416010-5
RE034009

TE Part #9-1879744-7
RP 1J 511R 0.1% 15PPM CUT LENGTH

TE Part #5-160465-1
250 FASTON REC 18-16 AWG BR

TE Part #5953497-5
S.C.READER 0.76mm PANEL MOUNT W CABLE

TE Part #1544550-1
MODULE AUTOFUSIBLE

Documents

Product Drawings

MTA-156 HDR.14P/13C

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_100656-1_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_100656-1_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_100656-1_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English