

Main

Range	Resi9
Product or component type	Remote indication auxiliary
Device short name	OF
Signal contacts composition	1 C/O
[In] rated current	0.017 A at 230 V, AC 50 Hz
9 mm pitches	2


Complementary

Range compatibility	Resi9 Resi9 XE ID Wiser Wiser Link EM5
Mounting mode	Clip-on
Mounting support	DIN rail
Height	81 mm
Width	18 mm
Depth	74 mm
Colour	White (RAL 9003)
Connections - terminals	Plug in (top) Screw clamp terminal (bottom)

Environment

Standards	EN/IEC 61008
IP degree of protection	IP20
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...40 °C

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins