

Deep groove ball bearings 624-2Z (Series 62...-2Z)

main dimensions to DIN 625-1, gap seals on both sides

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

| | |
|--------------------|------------------|
| d | 4 mm |
| D | 13 mm |
| B | 5 mm |
| | |
| D ₂ | 11,35 mm |
| d ₂ | 6 mm |
| Da max | 11,2 mm |
| da min | 5,8 mm |
| r _a max | 0,2 mm |
| r _{min} | 0,2 mm |
| | |
| m | 0,003 kg Mass |

| | | |
|----------------|-------------|-----------------------------------|
| C_r | 1380 N | Basic dynamic load rating, radial |
| C_{0r} | 485 N | Basic static load rating, radial |
| C_{ur} | 25,5 N | Fatigue limit load, radial |
| n_G | 61000 1/min | Limiting speed |
| $n_{\theta r}$ | 53000 1/min | Reference speed |
| f_0 | 12,2 | Calculation factor |



