

FEATURES

- Black polyester coated stainless steel
- Can be applied manually
- Releasable and re-usable – can be used more than once
- Specially designed for industrial applications in aggressive environments
- Flame retardant
- Highly durable with excellent chemical resistance

RS PRO Black Polyester Coated Stainless Steel Releasable Cable Tie, 230mm x 5 mm

RS Stock No.: 185-8686



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO stainless steel grade 316 coated releasable cable ties have been designed for use in Industrial and Marine environments. These ties are an ideal alternative where Nylon 66 cable ties are not suitable such as harsh environments or places where there is heat. The stainless steel used has a high resistance to damage by chemicals and salts making them suitable for harsh environments. The black polyester coating improves the handling properties of the stainless steel reducing the possibility of chaffing and blends with the colour of most cables

General Specifications

Type	Releasable
Colour	Black
Material	Polyester Coated Stainless Steel
Application	in industries such as: Oil and gas Marine Chemical Maintenance Automotive Solar Ship Building Mining Defence Services
Resistant To	Chemical and corrosion, radiation and abrasion
UV Resistant	Yes
Minimum Operating Temperature	-80°C
Maximum Operating Temperature	150°C
Fire Behaviour	Flame retardant , Halogen Free
Quantity	100

Mechanical Specifications

Length	330mm
Width	5mm
Tensile Strength	420N
Maximum Bundle Strength	95mm

Approvals

Standards Met	ABS, DNV, Lloyd's Register, UL
---------------	--------------------------------

**Dimensions**

RS Article	Colour	Length (mm)	Width (mm)	Quantity	Max Bundle Dia. (mm)
185-8670	Black	230	5	100	60
547-4399	Black	230	10	100	60
185-8686	Black	330	5	100	95
185-9364	Black	330	10	100	95
547-4406	Black	450	10	100	130