

PRODUCT-DETAILS

GSC281NP

OUTER SLEEVE ID .281 NICKEL PLATED



General Information

Extended Product Type	GSC281NP
Product ID	7TAI029980R0239
EAN	5415022252897
Catalog Description	OUTER SLEEVE ID .281 NICKEL PLATED
Long Description	Two Piece Outer Sleeve Connector for Hexagonal Range, Length 1/4 Inch/6.4mm, Inner Diameter .281 Inches/7.14mm, Outer Diameter .331 Inches/8.40mm, Color Purple, Soft Bronze, Nickel Plated

Ordering

EAN	5415022252897
UPC	786210950945

Dimensions

Product Net Length	0, mm
--------------------	-------

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	4.5 in 114 mm
Package Level 1 Height	3 in

	76 mm
Package Level 1 Depth / Length	6 in 152 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	21.5 in 546 mm
Package Level 2 Height	8.5 in 216 mm
Package Level 2 Depth / Length	3.43 in 87 mm

Additional Information

Application	for Grounding, Terminating and Insulating Shielded and Coaxial Cable
Brand / Label	Sta-Kon
Color	Purple
Effective Date	20050112
Material	Soft Bronze
Number of Batteries	0
Product Name	ELECTRICAL CONNECTOR, <1000V
Product Type	Two-Piece Outer Sleeve Connector

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	GSC281NP
Instructions and Manuals	GSC281NP

Classifications

ETIM 6	EC002650 - Connection for screened wires
ETIM 7	EC002650 - Connection for screened wires
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4603 >> Electrical terminals

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

