

plastic tubing PUN-3X0,5-SI

Part number: 152583

★ Core product range

FESTO



Data sheet

Feature	Value
Outside diameter	3 mm
Bending radius relevant for flow rate	12 mm
Inside diameter	2.1 mm
Min. bending radius	9 mm
Tubing characteristics	Suitable for energy chains in applications with high cycle rates
Tubing test conditions	Suitable for energy chains: > 5 million cycles to FN 942021
Temperature dependent operating pressure	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Material fire test	UL94 HB
Ambient temperature	-35 ... 60 °C
Authorisation	TÜV
Product weight according to length	0.0044 kg/m
Pneumatic connection	For push-in connector outside diameter 3 mm für Stecknippel Innen-Ø 2 mm
Colour	silver
Shore hardness	D 52 +/-3
Materials note	Free of copper and PTFE Conforms to RoHS
Material tubing	TPE-U(PU)