

MLFB-Ordering data

6SL3202-0AE23-8CA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

### Rated data

Rated current 39.00 A

Power loss 0.110 kW

### Mechanical data

Width 257.0 mm (10.12 in)

Height 235.0 mm (9.25 in)

Depth 114.7 mm (4.52 in)

Degree of protection IP20 / UL open type

Net weight 11.20 kg (24.69 lb)

### Connections

#### Power connection motor

Version screw terminals

Conductor cross-section 16.00 mm<sup>2</sup>

#### PE connection

Version M5 screw studs