

**BOSCH**

Invented for life

# Product data sheet

Power tools for trade & industry

Random Orbit Sander

## PRO GEX 185-LI



A well-balanced cordless sander for a superior finish and no more arm fatigue

### The most important data

Rated input power	0 W
Sanding pad diameter	125 mm
Orbit diameter	2.5 mm

**Order number** 0 601 3A5 020

## Technical data

### Additional data

Rated input power	0 W
Sanding pad diameter	125 mm
Orbit diameter	2.5 mm
Voltage, electrical	18 V
Weight	0.93 kg
No-load speed	6,000 – 10,000 rpm
Orbital stroke rate	12,000 – 20,000 opm
Eccentricity	1.25 mm
Sanding sheet / disc attachment	hook-and-loop fastening

## Noise/vibration information

### Sanding solid wood

Vibration emission value ah	2.2 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>



# Product data sheet

Power tools for trade & industry

---

## Advantages:

- Ideally positioned 18V battery for well-balanced sanding and no more arm fatigue
- Efficient brushless motor with consistent removal rate and a max run time 40 mins with GBA 4Ah battery
- Ergonomic design with low vibration up to 2.2 m/s<sup>2</sup> for comfortable sanding
- Ideal for sanding wood, wood materials, or plaster and removing paint



---

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/ao/en/wac/>

