

FEATURES

- Indicator light
- Telephone slide base
- 5,000 hr life
- Luminosity of 3.5 lm
- Voltage rating of 24V
- Current rating of 50mA
- Length of 44mm
- Diameter of 6.8mm
- Conforms to ANSI/ESD S20.20:2014 and BS EN 61340-5-1:2000 on electrostatic discharge

Telephone Slide Indicator Light, Clear, 24 V, 50 mA, 5000h

RS Stock No.: 294-5191



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Telephone slide lamps are commonly found in a variety of equipment, from garden lights to gambling machines. They are a durable and long-lasting way to illuminate.

This lamp from the RS PRO range will provide an energy-efficient 5,000 h of life, and gives a luminosity of 3.5 lm. It comprises a clear indicator light that operates at a voltage rating of 24 V and a current rating of 50 mA.

General Specifications

Lamp Base	Telephone Slide
Lamp Size	T6.8
Lens Colour	Clear
Luminosity	3.5lm
Life hours	5000h
Housing Material	Glass
Applications	Automotive industry; Gambling machine industry; Car indicator; Garden lights; Paper lanterns; Battery-powered flashlights

Electrical Specifications

Voltage Rating	24V
Current Rating	50mA
Light Output	3.5lm

Mechanical Specifications

Diameter	6.8mm
Length	44mm

Approvals

Compliance/Certifications

RoHS, ANSI/ESD S20.20:2014, BS EN 61340-5-1:200

