

3M™ Reusable Respirator Filters (Bayonet)

Technical Data Sheet

Product Description

The 3M™ Bayonet filters are designed to fit on all 3M™ reusable half and full face masks (except 6098 and 6099 which are full face only). There are 6 'families of filters' to choose from, depending upon your need.

Product Range

- 3M™ 2000 Series Particulate Filters
- 3M™ 5000 Series Particulate Filters
- 3M™ 6000 Series Particulate filters
- 3M™ 6000 Series Gas and Vapour filters
- 3M™ 6000 Series Gas, Vapour and particulate filters
- 3M™ 6000i Series Organic Gas and Vapour filters with 3M™ Service Life Indicator

Standard and Approvals

The 3M™ 2000, 5000 and 6000 Particulate filters meet the requirements of the European standard EN 143:2000 + A1:2006.

The 3M™ 6000 Gas and Vapour, Organic Gas and Vapour Service Life Indicator and Combination Gas, Vapour and Particulate filters meet the requirements of the European standard EN 14387:2004 + A1:2008.

The products are CE marked and certified by BSI Product Services. (Notified Body number 0086)

Cleaning and Storage

The product MUST NOT be immersed in water/liquid during cleaning. The plastic components of the filters may be wiped with a 3M™ 105 Face Seal Cleaner.

Use Limitations.

Replace 3M™ Particulate Filters when it becomes difficult to breathe comfortably (this will vary from individual to individual) or the filter becomes dirty or physical damage occurs 3M bayonet masks only.

Replace 3M™ Gas & Vapour filters in accordance with your established change schedule or government regulation, or sooner if the contaminant can be detected inside the respirator by smell or taste.



3M™ Reusable Respirator Filters (Bayonet) can only be used with 3M Respirators fitted with a bayonet connection, eg 3M™ Half Masks, 6000, 6500, 7000 and 7500 and 3M™ Full Face masks 6000 and 7907S.


Before use, check the expiration date. For other use limitations please refer to the User Information supplied with the products.

Composition	
3M™ 2000 Series	Polypropylene
3M™ 5000 Series	Polypropylene
3M™ 6000 Series Particulate filters	Filter Paper Polystyrene Polyethylene ABS (6098 only) Carbon
3M™ 6000 Series Gas and Vapour filters	Carbon Sorbent Polyester Polypropylene
3M™ 6000 Series Gas, Vapour and particulate filters	Carbon Sorbent Polyester Polypropylene Filter Paper
3M™ 6000i Series Organic Gas and Vapour filters with 3M™ Service Life Indicator	Carbon Sorbent Polyester Polypropylene Polyester Adhesive Specialty polymer


Shelf life: 5 year from production date when stored at storage conditions described on packaging.

*The shelf life as defined above remains a indicative and maximum data, subject to many external and non controllable factors. It may never be interpreted as a warranty.


3M™ Particulate Filters 2000 Series

Filter		Protection Level	Protection Against
2125		P2 R	Solid and Liquid particles
2128		P2 R	Solid and liquid particles, ozone protection(10 x OEL), nuisance level organic vapours/acid gas
2135		P3 R	Solid and Liquid particles
2138		P3 R	Solid and liquid particles, ozone protection(10 x OEL), nuisance level organic vapours/acid gas

3M™ Particulate Filters 5000 Series

Filter		Protection Level	Protection Against
5911		P1 R	Solid and Liquid particles
5925		P2 R	Solid and Liquid particles
5935		P3 R	Solid and Liquid particles







3M™ Particulate Filters 6000 Series

Filter		Protection Level	Protection Against
6035		P3 R	Solid and Liquid particles
6038		P3 R	Hydrogen Fluoride up to 10 x OEL with half masks or 30 ppm with full face, + relief from nuisance levels acid gases and organic vapours at levels below the OEL.





3M™ Particulate Accessories

501		Filter retainer
502		Filter retainer
603		Filter platform



3M™ Gas and Vapour Filters 6000 Series

Filter		Protection Level	Protection Against
6051		A1	Organic gases and vapours boiling point (bp) >65°C
6054		K1	Ammonia and derivatives
6055		A2	Organic vapours bp>65°C
6057		ABE1	Organic vapours bp>65°C, inorganic vapours and acid gases
6059		ABEK1	Organic vapours bp>65°C, inorganic vapours, acid gases ammonia and its derivatives
6075		A1+ formaldehyde	Organic vapours bp>65°C and formaldehyde

3M™ Gas, Vapour and Particulate Filters 6000 Series

Filter		Standard	Protection Level	Protection Against
6091		EN14387: 2004 +A1:2008	A1P3 R	Organic vapours (b.pt. >65°C), & Particulates
6092		EN14387: 2004 +A1:2008	ABEK1P3 R + Formaldehyde	Combination organic vapours (b.pt. >65°C), inorganic & acid gases, Ammonia Particulates and Formaldehyde
6095		EN14387: 2004 +A1:2008	A2P3 R	Organic vapours (b.pt. >65°C), & Particulates
6096		EN14387: 2004 +A1:2008	A1E1HgP3 R	Organic vapours, Acid gases(b.pt. >65°C), Mercury vapour, Chlorine & Particulates
6098*			AXP3 R	Organic Vapours (b.pt. < 65°C)
6099*			A2B2E2K2HgP3 R + Formaldehyde	Combination organic vapours (b.pt. >65°C), inorganic & acid gases, Ammonia, Mercury Particulates and Formaldehyde

3M™ Gas and Vapour Filters with 3M™ Service Life Indicator 6000i Series

Filter		Protection Level	Protection Against
6051i		A1	Organic gases and vapours bp>65°C
6055i		A2	Organic gases and vapours bp>65°C

* For use with 3M(TM) Fullface masks only.

IMPORTANT NOTICE

The use of the 3M product described within this document assumes that the user has previous experience of this type of product and that it will be used by a competent professional. Before any use of this product it is recommended to complete some trials to validate the performance of the product within its expected application.

All information and specification details contained within this document are inherent to this specific 3M product and would not be applied to other products or environment. Any action or usage of this product made in violation of this document is at the risk of the user.

Compliance to the information and specification relative to the 3M product contained within this document does not exempt the user from compliance with additional guidelines (safety rules, procedures). Compliance to operational requirements especially in respect to the environment and usage of tools with this product must be observed. The 3M group (which cannot verify or control those elements) would not be held responsible for the consequences of any violation of these rules which remain external to its decision and control.

Warranty conditions for 3M products are determined with the sales contract documents and with the mandatory and applicable clause, excluding any other warranty or compensation.

Respiratory Protection is only effective if it is correctly selected, fitted and worn throughout the time when the wearer is exposed to respiratory contaminants. 3M offers advice on the selection of products, and training in the correct fitting and usage.

For more information on 3M products and services please contact 3M.

Personal Safety Division
3M Centre
Cain Road, Bracknell
Berkshire RG12 8HT

www.3M.eu/safety

3M is a trademark of 3M Company.
Please recycle. Printed in the United Kingdom.
© 3M 2017. All rights reserved.
Rev 2017/01

