



E2E-X3D18 2M

Proximity sensor, inductive, brass-nickel, M8, shielded, 3 mm, NO, 2 m cable, DC 2-wire

Specifications

Size	M8
Mounting type	Quasi-flush
Sensing distance	3 mm
Overall length of sensor	37.8 mm
Thread length	21 mm
Material housing	Brass, nickel plated
Output type	2-wire
Operation mode	NO
Connection method	Cable
Cable specifications	PVC (oil-resistant)
Cable length	2 m
IO-Link function	×
Degree of protection (IP)	IP67/IP67G/IP69K

Accessories



Y92E-J8S12

Mounting Sleeves e-jig for M8 Prox

CAD Library



E2E NEXT Datasheet

EN PDF 40 MB



E2E(Q)-X_D_ Instruction Sheet

EN PDF 12.7 MB



IO-Link Series Brochure

EN PDF 6.41 MB