

G9

INSPECTION BEAM POCKET LIGHT

INSPECTION | 22M BEAM | 2H 30MIN



The G9 Flashlight features our Inspection Beam Optic that gives users a perfectly circular beam that has little glare, making optimal for up close work. Due to its small size and weight, it is an excellent choice for an everyday carry item. The light also possesses the versatility of a two-way clip, which allows for users to clip to a pocket or a bill of a hat. Built for ease of use, the light is activated by just twisting the end cap.

With Coast's commitment to quality, the G9 Flashlight is impact resistant, weather resistant and its LED is virtually unbreakable. The G6 Flashlight is backed by Coast's lifetime warranty against defects in materials and workmanship. Tested and rated to ANSI/FL1 standards.

BATTERY TYPE	1 x AAA (Alkaline)
BEAM DISTANCE (HIGH)	72 ft / 22 m
INCLUDED	1 x AAA Battery Two-way clip
LENGTH	4.1 in / 10.4 cm

LIGHT OUTPUT (HIGH)	Inspection Beam
RUNTIME (HIGH)	2 h 30 min
WEIGHT	2 oz / 57 g



INSPECTION BEAM OPTIC

Never miss a detail. The Inspection Beam cuts clean, consistent light from edge to edge to evenly illuminate work spaces. Engineered for pen lights that fit in the pocket, this beam simplifies up-close work and brightens hard-to-reach objects at up to 30 feet / 9 meters.



TWO-WAY CLIP

Store it away or shine it forward. The Two-Way Clip enables gives you flexibility to stash the light in your pocket or clip it to the brim of your hat.



WATER RESISTANCE

Don't worry about the weather. COAST lights that have passed the IPX4-level water resistance test are splash-resistant and built with durable materials that stand up to nature.