






















































































## Side clip on housing

Style	Ordering number	Cable entry			Description	Outline drawing dimensions in mm
		 PG	 PG	 PG		
<b>Surface-mounted housing</b> bottom entry						
		42.50.06.00			HB.6.AG-LB	
	51.42.50.06.00			HB-K.6.AG-LB		
<b>New!*</b> With locking flange						
	19.42.50.06.00			HB-R.6.AG-LB	Panel cut-out 	
	59.42.50.06.00			HB-K/R.6.AG-LB		
<b>With cover</b>						
	42.52.06.00			HB.6.AGD-LB	<b>*New!</b> Surface mounted housings (side entry) with locking flange for HD-DSTV-RA and DSTVK-RA inserts with locking clip for reverse mounting and screw mounting from the front side.	
	51.42.52.06.00			HB-K.6.AGD-LB		
<b>New!*</b> With locking flange						
	19.42.52.06.00			HB-R.6.AGD-LB		
	59.42.52.06.00			HB-K/R.6.AGD-LB		

## Side cup on housing

Style	Ordering number	Cable entry			Description	Outline drawing dimensions in mm	
		 PG	 PG	 PG			
<b>Hood</b> side entry standard construction							
	42.60.06.05	16			HB.6.SG-LB.1.16 HB.6.SG-LB.1.16.Z HB.6.SG-LB.2.16 HB.6.SG-LB.2.16.Z		
	42.60.06.79		16				
	42.60.06.06	2x16			HB-K.6.SG-LB.1.16 HB-K.6.SG-LB.1.16.Z HB-K.6.SG-LB.2.16 HB-K.6.SG-LB.2.16.Z		
	42.60.06.95		2x16				
	51.42.60.06.05	16			HB-K.6.SG-LB.1.16 HB-K.6.SG-LB.1.16.Z HB-K.6.SG-LB.2.16 HB-K.6.SG-LB.2.16.Z		
	51.42.60.06.79		16				
	51.42.60.06.06	2x16			HB-K.6.SG-LB.1.16 HB-K.6.SG-LB.1.16.Z HB-K.6.SG-LB.2.16 HB-K.6.SG-LB.2.16.Z		
	51.42.60.06.95		2x16				
high construction							
	49.60.16.07	21			HD.16.SG-LB.1.21 HD.16.SG-LB.1.21.Z HD.16.SG-LB.2.21 HD.16.SG-LB.2.21.Z		
	49.60.16.80		21				
	49.60.16.08	2x21			HD-K.16.SG-LB.1.21 HD-K.16.SG-LB.1.21.Z HD-K.16.SG-LB.2.21 HD-K.16.SG-LB.2.21.Z		
	49.60.16.96		2x21				
	49.60.16.09	29			HD.16.SG-LB.1.29 HD.16.SG-LB.1.29.Z HD.16.SG-LB.2.29 HD.16.SG-LB.2.29.Z		
	49.60.16.81		29				
	49.60.16.48	2x29			HD-K.16.SG-LB.1.29 HD-K.16.SG-LB.1.29.Z HD-K.16.SG-LB.2.29 HD-K.16.SG-LB.2.29.Z		
	49.60.16.97		2x29				
	51.49.60.16.07	21			HD-K.16.SG-LB.1.21 HD-K.16.SG-LB.1.21.Z HD-K.16.SG-LB.2.21 HD-K.16.SG-LB.2.21.Z		
	51.49.60.16.80		21				
	51.49.60.16.08	2x21			HD-K.16.SG-LB.1.21 HD-K.16.SG-LB.1.21.Z HD-K.16.SG-LB.2.21 HD-K.16.SG-LB.2.21.Z		
	51.49.60.16.96		2x21				
	51.49.60.16.09	29			HD-K.16.SG-LB.1.29 HD-K.16.SG-LB.1.29.Z HD-K.16.SG-LB.2.29 HD-K.16.SG-LB.2.29.Z		
	51.49.60.16.81		29				
	51.49.60.16.48	2x29			HD-K.16.SG-LB.1.29 HD-K.16.SG-LB.1.29.Z HD-K.16.SG-LB.2.29 HD-K.16.SG-LB.2.29.Z		
	51.49.60.16.97		2x29				
With cover standard construction							
	42.62.06.05	16			HB.6.SGD-LB.1.16 HB.6.SGD-LB.1.16.Z HB.6.SGD-LB.2.16 HB.6.SGD-LB.2.16.Z		
	42.62.06.79		16				
	42.62.06.06	2x16			HB-K.6.SGD-LB.1.16 HB-K.6.SGD-LB.1.16.Z HB-K.6.SGD-LB.2.16 HB-K.6.SGD-LB.2.16.Z		
	42.62.06.95		2x16				
	51.42.62.06.05	16			HB-K.6.SGD-LB.1.16 HB-K.6.SGD-LB.1.16.Z HB-K.6.SGD-LB.2.16 HB-K.6.SGD-LB.2.16.Z		
	51.42.62.06.79		16				
	51.42.62.06.06	2x16			HB-K.6.SGD-LB.1.16 HB-K.6.SGD-LB.1.16.Z HB-K.6.SGD-LB.2.16 HB-K.6.SGD-LB.2.16.Z		
	51.42.62.06.95		2x16				
high construction							
	49.62.16.07	21			HD.16.SGD-LB.1.21 HD.16.SGD-LB.1.21.Z HD.16.SGD-LB.2.21 HD.16.SGD-LB.2.21.Z		
	49.62.16.80		21				
	49.62.16.08	2x21			HD-K.16.SGD-LB.1.21 HD-K.16.SGD-LB.1.21.Z HD-K.16.SGD-LB.2.21 HD-K.16.SGD-LB.2.21.Z		
	49.62.16.96		2x21				
	49.62.16.09	29			HD.16.SGD-LB.1.29 HD.16.SGD-LB.1.29.Z HD.16.SGD-LB.2.29 HD.16.SGD-LB.2.29.Z		
	49.62.16.81		29				
	49.62.16.48	2x29			HD-K.16.SGD-LB.1.29 HD-K.16.SGD-LB.1.29.Z HD-K.16.SGD-LB.2.29 HD-K.16.SGD-LB.2.29.Z		
	49.62.16.97		2x29				
	51.49.62.16.07	21			HD-K.16.SGD-LB.1.21 HD-K.16.SGD-LB.1.21.Z HD-K.16.SGD-LB.2.21 HD-K.16.SGD-LB.2.21.Z		
	51.49.62.16.80		21				
	51.49.62.16.08	2x21			HD-K.16.SGD-LB.1.21 HD-K.16.SGD-LB.1.21.Z HD-K.16.SGD-LB.2.21 HD-K.16.SGD-LB.2.21.Z		
	51.49.62.16.96		2x21				
	51.49.62.16.09	29			HD-K.16.SGD-LB.1.29 HD-K.16.SGD-LB.1.29.Z HD-K.16.SGD-LB.2.29 HD-K.16.SGD-LB.2.29.Z		
	51.49.62.16.81		29				
	51.49.62.16.48	2x29			HD-K.16.SGD-LB.1.29 HD-K.16.SGD-LB.1.29.Z HD-K.16.SGD-LB.2.29 HD-K.16.SGD-LB.2.29.Z		
	51.49.62.16.97		2x29				