



## PASE50-XL-N-FA125

Plummer block housing unit

Plummer block housing units PASE...-FA125, cast iron housing, radial insert ball bearing with eccentric locking collar, P seals, with anti-corrosion protection

X-life

### Technical information



### Your current product variant

Material	GG	Grey cast iron
Groove	N	Cast iron housing with undercut slot for end caps

### Main Dimensions & Performance Data

d	50 mm	Bore diameter
L	200 mm	Length total
H 2	115 mm	Height
≈m	2.63 kg	Weight

### Mounting dimensions

J	158 mm	Distance fixing bore
N	18 mm	Width (slot)
N 1	23 mm	Length (slot)



Dimensions

H	57.2 mm	Distance shaft axis
A	54 mm	Width (base)
A <sub>1</sub>	34 mm	Width (head)
H <sub>1</sub>	21.5 mm	Heigth (base)
B <sub>1</sub>	43.8 mm	Locking collar total width
S <sub>1</sub>	32.8 mm	Distance of raceway to locking collar
Q	M6	Connection thread for lubrication

Additional information

ASE10-FA125	Housing
GRAE50-XL-NPP-B-FA125	Bearing designation
KASK10	Protecting cap

Temperature range

T <sub>min</sub>	-20 °C	Operating temperature min.
T <sub>max</sub>	120 °C	Operating temperature max.