



PW3 HI-VIS WORK TROUSERS

DESCRIPTION

Constructed using premium HiVisTex Pro tape and durable polyester/cotton fabric, this contemporary Hi-Vis Work Trousers provides ultimate wearer comfort. Oxford fabric reinforcement at key abrasion points and triple stitching throughout guarantees maximum durability. This trouser features top loading kneepad pockets and an easy access multiway thigh pocket for secure storage of your phone, keys and tools.

COMPOSITION

-  **Titanmill Plus: 65% Polyester, 35% Cotton, 300g**
-  **100% Polyester, 600D Oxford, PU Coated, 210g**
-  **Orange/Navy 28-48**

FEATURES

- Durable polycotton fabric with Texpel stain resistant finish
- Texpel™ Stain Eco a premium stain resistant finish to repel grime and water
- High rise back waistband ensures protection in all working positions
- Easy access cargo pocket
- Extendable leg length (31" to 33")
- Free pair of kneepads included with this trouser
- Triple-stitched seams for extra durability
- 2 Side pockets
- Two back patch pockets
- Double rule pocket
- D-ring for keys or ID cards
- Hammer loop for secure storage of work tools

STANDARDS

EN ISO 20471 Class 2
RIS 3279 TOM Issue 2 (Orange Only)
EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)
ANSI/ISEA 107 SUPPLEMENTAL CLASS E

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
PW340ONR	ORANGE/NAVY	28-14

FEATURES



TOP-LOADING KNEE PAD POCKETS
Top-loading knee pad pockets for quick and easy access



HALF ELASTICATED WAIST
Half elasticated waist for a secure and comfortable fit



HEAT APPLIED SEGMENTED REFLECTIVE TAPE
This symbol indicates that the garment has heat applied reflective tape



STANDARDS



EN ISO 20471
High Visibility Clothing - Test Methods
And Requirements



PERFORMANCE WORKWEAR
PW3™ contemporary workwear blends
sports and lifestyle trends with function,
a modern fit and improved comfort.

GET THE
COLLECTION



TECHINCAL INFORMATION



SATRA Technology Europe Ltd
(Notified Body Number.: NB: 2777) Bracetown
Business Park Clonree Dublin 15 D15 YN2P, Ireland
Cert No: 2777/14048-03/E00-00

Wash garment inside out and fully fastened

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m³)	EAN13	GTIN/DUN14
PW340ONR28	Orange/Navy	65	45	36	.960	5850.000	5036108307555	15036108796639
PW340ONR30	Orange/Navy	65	45	36	.960	5850.000	5036108307562	15036108796646
PW340ONR32	Orange/Navy	65	45	36	.998	5850.000	5036108307579	15036108796653
PW340ONR33	Orange/Navy	65	45	36	1.016	5850.000	5036108307586	15036108796660
PW340ONR34	Orange/Navy	65	45	36	1.028	5850.000	5036108307593	15036108796677
PW340ONR36	Orange/Navy	65	45	36	1.044	5850.000	5036108307609	15036108796684
PW340ONR38	Orange/Navy	65	45	36	1.066	5850.000	5036108307616	15036108796691
PW340ONR40	Orange/Navy	65	45	36	1.070	5850.000	5036108307623	15036108796707
PW340ONR41	Orange/Navy	65	45	36	1.080	5850.000	5036108307630	15036108796714
PW340ONR42	Orange/Navy	65	45	36	1.090	5850.000	5036108307647	15036108796721
PW340ONR44	Orange/Navy	65	45	36	1.110	5850.000	5036108307654	15036108796738
PW340ONR46	Orange/Navy	65	45	36	1.130	5850.000	5036108307661	15036108796745
PW340ONR48	Orange/Navy	65	45	36	1.140	5850.000	5036108307678	15036108796752