

Cable D-Sub/end sleeve shie. 32x0.34 8m

connection cable shielded f. SIMATIC ET200 SP HA from 37-pole D-sub to bare ends with wire end sleeve labeled 32 channels L = 8 m, 0.34 mm²



target system	SIMATIC ET 200SP HA
suitability for use	I/O modules
product type designation	Modular connection
product designation	Pre-assembled round cable
Operating data / header	
operating voltage / at DC	
• rated value	24 V
• maximum	60 V
ambient temperature	
• during operation	-30 ... +70 °C
• during storage	-30 ... +70 °C
General data / header	
suitability for interaction	
• input card PLC	Yes
• PLC output card	Yes
suitability for use	
• digital signal transmission	Yes
• analog signal transmission	Yes
Product properties, functions, components / general / header	
number of channels	32
design of cable	Round cable
wire length	8 m
number of poles	32
number of conductors / of connection cable	32
conductor cross section / rated value	0.34 mm ²
color / of cable sheath	Black
outer diameter / of cable sheath	11 mm
material / of the connection cable sheath	PVC
marking / of cores	label clip
design of the shield	braided shield
connector type	D-Sub connector
type of electrical connection / on enclosure	Female header
number of poles / at the 1st interface	37; control page
type of electrical connection / in the field	End sleeve
number of poles / at the 2nd interface	32; numbered
certificate of suitability	
• cULus approval	No
reference code / according to IEC 81346-2	WG
net weight	0.7 kg
last modified:	4/9/2025

