

Roll, Multi-Core Flat, Multi-Colour - TU TU0604-14G-X169

Datasheet

General Series Information

- Applicable tubing O.D.: Ø 2 to Ø 12 mm
- Number of cores: 2 to 6
- 8 colour variations.

Standard specifications

Tubing Size (O.D. x I.D.)	O.D. Ø6 x I.D. Ø4
Colour 1	1 (Black)
Colour 2	4 (Blue)
Colour 3	None
Colour 4	None
Colour 5	None
Colour 6	None
Tube Length per Roll	G (20 m)
Multi-core, Multi-colour Specification	X169 (2 Cores, roll)
-	Air
Maximum operating pressure	0.8 MPa

Additional information

Catalogue

[Flat_tubing_EU.pdf](#)