

306A - CLICK WRENCHES WITH REMOVABLE RATCHET | R.301A



Description

- Factory accuracy: $\pm 2\%$ except:
 - R.306-25D - K306-600D - K306-1000D ($\pm 4\%$).
 - R.304DA ($\pm 6\%$).
- Reliability of mechanism: 50 000 cycles (wrenches up to 200 N.m).
- Use possible with accessories:
 - End fitting: 9 x 12 or 14 x 18 mm.
 - Diameter: 30 mm.
- One-way wrenches usable for unscrewing by reversing the bits.
- Numbered wrenches supplied with ISO 6789 calibration certificate.
- Supplied in a plastic box with ratchet and hinged handle (except Ref R.306A25 - R.301A - K.306A600 - K.306A1000).

Information

L [mm]	185
Attachment	9 x 12
Box	BP.102
Capacity [N.m]	1 - 5
Wrench	R.304DA
Ratchet	R.372
Contents	Box
Graduation [N.m]	0,05
Knob	-
[g]	290