Features

- PVC Insulated
- Tin Plated
- Heat resistant: -10~75℃

RS PRO Butt Crimps

RS Stock No.: 0866316



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

PVC insulated butt terminals provide a fast, dependable, and professional solution for joining two wires end-to-end. Manufactured from high-conductivity copper and finished with corrosion-resistant tin plating, these connectors deliver excellent electrical performance and long-lasting reliability in demanding environments.

Designed for quick crimp installation, the seamless barrel construction ensures strong mechanical retention and maximum current flow, while the precision-engineered wire-stop helps position conductors correctly for consistent and secure crimps. Suitable for automotive, marine, industrial, electrical, and household wiring applications, these connectors help create durable wire splices without soldering.

General Specifications

Type	Easy Entry
Connector Type	Butt
Contact Plating	Tin
Contact Material	Copper
Crimp Tool Type	Crimping Pliers
Handle Cover Material	PVC

Type	Application for Cable Size		Stripped Length (mm)	Dimension(mm)		
	mm²	A.W.G.		L	D	d1
●	0.5-1.5	22-16	7.3-7.7	24.5	4.3	1.7
●	1.5-2.5	16-14	7.3-7.7	24.5	4.8	2.3
●	4-6	12-10	7.3-7.7	27	6.7	3.4

Operation Environment Specifications

Temperature Rating	-10°C to 75°C

Approvals

Compliance/Certifications	REACH / RoHS

