

**Sub-base**  
**VMPA-FB-AP-1-EMM-P5-SK**  
Part number: 8161059



 [General operating condition](#)

**Data sheet**

| Feature                        | Value                   |
|--------------------------------|-------------------------|
| Width                          | 42 mm                   |
| Length                         | 107.3 mm                |
| Grid dimension                 | 41 mm                   |
| Max. number of valve positions | 4                       |
| Operating pressure             | -0.09 MPa ... 1 MPa     |
| Operating pressure             | -0.9 bar ... 10 bar     |
| Pilot pressure                 | 0.3 MPa ... 0.8 MPa     |
| Pilot pressure                 | 3 bar ... 8 bar         |
| Corrosion resistance class CRC | 0 - No corrosion stress |
| LABS (PWIS) conformity         | VDMA24364 zone III      |
| Storage temperature            | -20 °C ... 60 °C        |
| Ambient temperature            | -5 °C ... 50 °C         |
| Product weight                 | 175 g                   |
| Pneumatic connection, port 1   | G1/4                    |
| Note on materials              | RoHS compliant          |
| Material sub-base              | Die-cast aluminium      |