



PRODUCT-DETAILS

SPL40/25M  
OIL RES UR LIQ.TIGHT NC40 25MT BLK



| 概要信息        |                                                                                                                                                                                                                                                   |
|-------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 产品型号        | SPL40/25M                                                                                                                                                                                                                                         |
| 产品ID        | 7TCA296030R0270                                                                                                                                                                                                                                   |
| 欧洲商品编号(EAN) | 5020963000973                                                                                                                                                                                                                                     |
| 目录说明        | OIL RES UR LIQ.TIGHT NC40 25MT BLK                                                                                                                                                                                                                |
| 详细描述        | Liquid Tight, Oil Resistant, Medium Flexiblility Conduit, 1-1/4 Inch, Nominal Conduit Size 40mm, Outside Diameter 41.8mm, Inside Diameter 35.4mm, Static Bend Radius 180mm, Reel Length 25 Meters, PVC Covering with Galvanised Steel Core, Black |

| 其他信息   |                                                      |
|--------|------------------------------------------------------|
| 应用     | Liquid Tight - Indoors / Outdoors, Marine, Buildings |
| 产品应用类型 | Oil Resistant Conduit                                |

| 订货信息        |               |
|-------------|---------------|
| 欧洲商品编号(EAN) | 5020963000973 |
| UPC         | 786210247243  |

|      |      |
|------|------|
| 尺寸   |      |
| 产品净深 | 25 m |

|                     |                                         |
|---------------------|-----------------------------------------|
| 技术参数                |                                         |
| Number of Batteries | 0                                       |
| 颜色                  | Black                                   |
| 材料                  | Galvanized Steel Core with PVC Covering |

|         |                           |
|---------|---------------------------|
| 环境条件    |                           |
| WEEE 类别 | Product Not in WEEE Scope |

|        |                    |
|--------|--------------------|
| 包装信息   |                    |
| 1级包装单元 | 1 piece            |
| 1级包装高度 | 10.62 in<br>270 mm |
| 1级包装长度 | 32.28 in<br>820 mm |
| 1级包装宽度 | 32.28 in<br>820 mm |

|                   |                 |
|-------------------|-----------------|
| 认证及声明（文件编码）       |                 |
| 数据手册，技术资料         | SPL40/25M       |
| 说明书和手册            | SPL40/25M       |
| 符合性声明 - CE        | 9AKK107492A9618 |
| RoHS信息            | 9AKK107992A8994 |
| RoHS日期            | 9AKK107992A8994 |
| REACH Declaration | 9AKK107992A8994 |

|        |                                     |
|--------|-------------------------------------|
| 分类     |                                     |
| ETIM 8 | EC001179 - Protective metallic hose |
| UNSPSC | 39131706                            |

|    |  |
|----|--|
| 分类 |  |
|----|--|

低压产品及系统 → 安装产品 → 电缆保护、防爆和照明 → Flexible Cable Protection Systems

