

Datasheet

Fibre Optic Cable

Premise Distribution Cable

RS Stock No: 290-8861



A premise distribution cable constructed around 900µm tight buffered elements, suitable for direct termination.

- Low smoke zero halogen (LSZH)
- Compact
- Excellent tensile performance
- 5.30mm diameter
- 1000N maximum tensile load
- 53mm minimum static bend
- 80mm minimum dynamic bend
- Fire: IEC 60332-1
- Temp. – Operation -20°C to +60°C
- Temp. – Storage -20°C to +60°C
- Temp. - Installation -10°C to +60°C