

BIZ7 - Bizflame Work Hi-Vis Contrast FR

Coverall

Collection: Bizflame™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizflame Work HV: 99% Cotton, 1% Carbon Fibre, 330g

Outer Carton: 10

Product information

Bizflame Work Hi-Vis Anti-Static Coverall offers all the benefits of flame resistant fabric with added high visibility and anti-static protection.

Bizflame™ Work

BizFlame™ Work has been developed and designed using the highly innovative Bizflame™ Work flame resistant fabric with added anti-static properties. Certified to a range of international standards.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E3, F1)

EN ISO 11611 Class 1 (A1+A2)

EN 1149 -5

EN ISO 20471 Class 3



Features

- Protection against radiant, convective and contact heat
- Certified protection against molten metal splash
- Rule pocket
- Quick and easy side access
- Stud adjustable cuffs for a secure fit
- Concealed stud front for easy access
- Twin-stitched seams for extra durability
- Two tier knee pad pockets allowing two positioning options
- Premium sew on flame resistant reflective tape
- 8 pockets for ample storage
- Radio loops for easy clipping of a radio

BIZ7 - Bizflame Work Hi-Vis Contrast FR Coverall
Commodity Code: 6203425100

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/14078-02/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
BIZ7YNRS	Yellow/Navy	58.0	38.0	26.0	1.4300	0.0573	5036108188741	15036108675859
BIZ7YNRM	Yellow/Navy	58.0	38.0	26.0	1.2100	0.0573	5036108188734	15036108675842
BIZ7YNRL	Yellow/Navy	58.0	38.0	26.0	1.1900	0.0573	5036108188727	15036108675835
BIZ7YNRXL	Yellow/Navy	58.0	38.0	28.0	1.6500	0.0617	5036108188758	15036108675866
BIZ7YNRXXL	Yellow/Navy	58.0	38.0	28.0	1.6800	0.0617	5036108188765	15036108675873
BIZ7YNRXXXL	Yellow/Navy	58.0	38.0	28.0	1.6900	0.0617	5036108188772	15036108675880
BIZ7YNR4XL	Yellow/Navy	58.0	38.0	28.0	1.7300	0.0617	5036108204496	15036108693013