



verso mobile workstand with full cupboard. Featuring a robust, steel channel, framework with 100mm diameter castors and a 30mm lino worktop. Cupboard - WxDxH: 525x550x600mm. with single, reinforced 525mm door and 1 adjustable height, galvanised steel shelf (75kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 5010 gentian blue. WxDxH: 700x600x930mm.

Breite [mm]: 700
Tiefe [mm]: 600
Höhe [mm]: 930
Bruttogewicht [kg]: 54.02
EAN-Code: 5039350034224
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Gentian blue
Main RAL colour	RAL 5010
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	verso
---------------	-------

Schrank, Gehäuse, Werkbank und EAP

Worktop/housing top type	Lino
Shelf load capacity [kg]	75
Door type	Plain
Door height 1 [mm]	525